

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293268

Luminaire Tested: P3AS09R40W2N902750DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902750DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 521.0 lumens
Efficiency: N/A
Efficacy: 57.9 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293268
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293268

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116964
5°	114836
10°	108237
15°	98321
20°	86364
25°	73770
30°	61098
35°	47114
40°	33549
45°	22607
50°	12315
55°	8678
60°	8201
65°	7575
70°	6732
75°	6439
80°	5177
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22607 cd/sqm



TEST NUMBER: P1293268
 CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.7	9.3
10°-20°	120.6	23.2
20°-30°	139.5	26.8
30°-40°	109.9	21.1
40°-50°	56.4	10.8
50°-60°	21.6	4.1
60°-70°	14.3	2.7
70°-80°	7.8	1.5
80°-90°	2.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.8	59.3
0°-40°	418.7	80.4
0°-60°	496.7	95.3
0°-90°	521.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	521.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	533	
5°	522	49
15°	433	121
25°	305	139
35°	176	110
45°	73	56
55°	23	22
65°	15	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1293268
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	533.4
2.5°	530.4
5°	521.7
7.5°	506.5
10°	486.1
12.5°	462.2
15°	433.1
17.5°	402.8
20°	370.1
22.5°	336.9
25°	304.9
27.5°	272.8
30°	241.3
32.5°	209.3
35°	176.0
37.5°	145.1
40°	117.2
42.5°	93.3
45°	72.9
47.5°	53.0
50°	36.1
52.5°	26.2
55°	22.7
57.5°	20.4
60°	18.7
62.5°	16.3
65°	14.6
67.5°	12.2
70°	10.5
72.5°	8.7
75°	7.6
77.5°	5.8
80°	4.1
82.5°	3.5
85°	1.7
87.5°	1.2
90°	0.0

(END OF REPORT)