

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293277

Luminaire Tested: P3AS09R40W2N902750DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293277
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902750DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 190.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293277
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293277
 CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80	80	80	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59162
5°	57957
10°	53974
15°	47038
20°	37897
25°	28405
30°	19978
35°	13090
40°	7929
45°	4745
50°	2831
55°	2256
60°	2061
65°	1764
70°	1667
75°	1356
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4745 cd/sqm



TEST NUMBER: P1293277

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.5	12.9
10°-20°	57.1	30.0
20°-30°	53.8	28.3
30°-40°	31.1	16.4
40°-50°	12.4	6.5
50°-60°	5.5	2.9
60°-70°	3.4	1.8
70°-80°	1.8	0.9
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	135.3	71.2
0°-40°	166.4	87.6
0°-60°	184.3	97.0
0°-90°	190.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	190.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	270	
5°	263	24
15°	207	57
25°	117	54
35°	49	31
45°	15	12
55°	6	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1293277
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	269.8
2.5°	268.2
5°	263.3
7.5°	254.3
10°	242.4
12.5°	226.3
15°	207.2
17.5°	185.7
20°	162.4
22.5°	139.2
25°	117.4
27.5°	97.3
30°	78.9
32.5°	62.9
35°	48.9
37.5°	37.0
40°	27.7
42.5°	20.7
45°	15.3
47.5°	11.1
50°	8.3
52.5°	6.7
55°	5.9
57.5°	5.4
60°	4.7
62.5°	3.9
65°	3.4
67.5°	2.8
70°	2.6
72.5°	2.1
75°	1.6
77.5°	1.3
80°	1.0
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)