

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291552

Luminaire Tested: P3AS09R15W2N902750DE010 E3D1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291552
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902750DE010 E3D1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 668.0 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291552
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291552
 CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100		98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97		96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95		94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93		92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92		91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90		89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89		88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87		86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86		85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1298427
5°	1088221
10°	512593
15°	154553
20°	57172
25°	22235
30°	8280
35°	2543
40°	916
45°	496
50°	375
55°	421
60°	482
65°	259
70°	321
75°	424
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 496 cd/sqm



TEST NUMBER: P1291552

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	382.2	57.2
10°-20°	227.2	34.0
20°-30°	47.7	7.1
30°-40°	7.7	1.2
40°-50°	1.3	0.2
50°-60°	1.0	0.1
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	657.1	98.4
0°-40°	664.8	99.5
0°-60°	667.1	99.9
0°-90°	668.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	668.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5921	
5°	4944	382
15°	681	227
25°	92	48
35°	10	8
45°	2	1
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1291552
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3D1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5921.3
1°	5902.8
2°	5808.8
3°	5620.8
4°	5345.1
5°	4943.8
6°	4472.2
7°	3932.9
8°	3418.0
9°	2835.0
10°	2302.1
12.5°	1242.1
15°	680.8
17.5°	398.7
20°	245.0
22.5°	150.0
25°	91.9
27.5°	55.5
30°	32.7
32.5°	18.5
35°	9.5
37.5°	5.3
40°	3.2
42.5°	2.1
45°	1.6
47.5°	1.1
50°	1.1
52.5°	1.1
55°	1.1
57.5°	1.1
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)