

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293278

Luminaire Tested: P3AS09R40W2N902750DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902750DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 210.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293278
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293278

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80	80	80	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69	69	69	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65	65	65	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65389
5°	64076
10°	59652
15°	51987
20°	41887
25°	31405
30°	22079
35°	14455
40°	8759
45°	5241
50°	3104
55°	2523
60°	2237
65°	1920
70°	1859
75°	1440
80°	1389
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5241 cd/sqm



TEST NUMBER: P1293278

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.0	12.9
10°-20°	63.1	30.0
20°-30°	59.4	28.3
30°-40°	34.4	16.4
40°-50°	13.7	6.5
50°-60°	6.0	2.9
60°-70°	3.7	1.8
70°-80°	2.0	0.9
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.5	71.2
0°-40°	183.9	87.6
0°-60°	203.7	97.0
0°-90°	210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	210.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	298	
5°	291	27
15°	229	63
25°	130	59
35°	54	34
45°	17	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1293278
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	298.2
2.5°	296.5
5°	291.1
7.5°	281.0
10°	267.9
12.5°	250.2
15°	229.0
17.5°	205.3
20°	179.5
22.5°	153.8
25°	129.8
27.5°	107.5
30°	87.2
32.5°	69.5
35°	54.0
37.5°	40.9
40°	30.6
42.5°	22.9
45°	16.9
47.5°	12.3
50°	9.1
52.5°	7.4
55°	6.6
57.5°	6.0
60°	5.1
62.5°	4.3
65°	3.7
67.5°	3.1
70°	2.9
72.5°	2.3
75°	1.7
77.5°	1.4
80°	1.1
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)