

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293281

Luminaire Tested: P3AS09R40W2N902750DE010 E3DLP1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293281  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902750DE010 E3DLP1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 212.0 lumens  
Efficiency: N/A  
Efficacy: 23.6 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293281  
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293281  
 CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	95	95	95	93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	88	88	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	81	81	81	80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	76	76	76	74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	71	71	71	69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	66	66	66	65
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	62	62	62	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	59	59	59	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	56	56	56	54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	53	53	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	66003
5°	64671
10°	60208
15°	52486
20°	42307
25°	31695
30°	22282
35°	14616
40°	8845
45°	5272
50°	3138
55°	2523
60°	2281
65°	1972
70°	1859
75°	1440
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5272 cd/sqm



TEST NUMBER: P1293281  
 CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	27.3	12.9
10°-20°	63.7	30.0
20°-30°	60.0	28.3
30°-40°	34.7	16.4
40°-50°	13.8	6.5
50°-60°	6.1	2.9
60°-70°	3.8	1.8
70°-80°	2.0	0.9
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.0	71.2
0°-40°	185.7	87.6
0°-60°	205.6	97.0
0°-90°	212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	212.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	301	
5°	294	27
15°	231	64
25°	131	60
35°	55	35
45°	17	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1293281  
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLP1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	301.0
2.5°	299.3
5°	293.8
7.5°	283.7
10°	270.4
12.5°	252.5
15°	231.2
17.5°	207.2
20°	181.3
22.5°	155.3
25°	131.0
27.5°	108.5
30°	88.0
32.5°	70.1
35°	54.6
37.5°	41.3
40°	30.9
42.5°	23.1
45°	17.0
47.5°	12.4
50°	9.2
52.5°	7.5
55°	6.6
57.5°	6.1
60°	5.2
62.5°	4.3
65°	3.8
67.5°	3.2
70°	2.9
72.5°	2.3
75°	1.7
77.5°	1.4
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)