

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291583

Luminaire Tested: P3AS09R15W2N902750DE010 E3DL1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291583  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R15W2N902750DE010 E3DL1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 605.0 lumens  
Efficiency: N/A  
Efficacy: 67.2 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291583  
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291583

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	93	93	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	88	88	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	85	85	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	81	81	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	78	78	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	75	75	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	73	73	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	70	70	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	68	68	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	516823
5°	458771
10°	318587
15°	188401
20°	107296
25°	61334
30°	33929
35°	18096
40°	10019
45°	5427
50°	3377
55°	2676
60°	2281
65°	2127
70°	1859
75°	1949
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5427 cd/sqm



TEST NUMBER: P1291583

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	177.2	29.3
10°-20°	233.9	38.7
20°-30°	120.4	19.9
30°-40°	45.2	7.5
40°-50°	14.8	2.4
50°-60°	6.4	1.1
60°-70°	4.0	0.7
70°-80°	2.4	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.6	87.9
0°-40°	576.8	95.3
0°-60°	597.9	98.8
0°-90°	605.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2357	
5°	2084	177
15°	830	234
25°	254	120
35°	68	45
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1291583  
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DL1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2356.9
1°	2352.3
2°	2321.4
3°	2262.5
4°	2185.0
5°	2084.2
6°	1969.9
7°	1844.6
8°	1705.3
9°	1567.8
10°	1430.8
12.5°	1100.9
15°	829.9
17.5°	621.3
20°	459.8
22.5°	343.3
25°	253.5
27.5°	184.8
30°	134.0
32.5°	95.0
35°	67.6
37.5°	48.4
40°	35.0
42.5°	25.1
45°	17.5
47.5°	12.8
50°	9.9
52.5°	8.2
55°	7.0
57.5°	5.8
60°	5.2
62.5°	4.7
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.9
75°	2.3
77.5°	1.7
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)