

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293315

Luminaire Tested: P3AS09R40W2N902765DE010 E3CB1MMS\_3500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1293315  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902765DE010 E3CB1MMS\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 90CRI ,  
E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 831.1 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293315  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3CB1MMS\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293315  
 CATALOG NUMBER: P3AS09R40W2N902765DE010 E3CB1MMS\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85		
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82		
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79		
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76		
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73		
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	437553
5°	435438
10°	421257
15°	372692
20°	243154
25°	86134
30°	18256
35°	6023
40°	2204
45°	744
50°	614
55°	688
60°	526
65°	623
70°	385
75°	508
80°	758
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 1008 cd/sqm



TEST NUMBER: P1293315

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3CB1MMS\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.1	22.4
10°-20°	433.5	52.2
20°-30°	188.1	22.6
30°-40°	17.3	2.1
40°-50°	2.5	0.3
50°-60°	1.5	0.2
60°-70°	1.1	0.1
70°-80°	0.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	807.7	97.2
0°-40°	825.1	99.3
0°-60°	829.1	99.8
0°-90°	831.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	831.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1995	
5°	1978	186
15°	1642	433
25°	356	188
35°	22	17
45°	2	2
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293315  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3CB1MMS\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1995.4
2.5°	1993.0
5°	1978.2
7.5°	1946.9
10°	1891.9
12.5°	1799.0
15°	1641.7
17.5°	1380.9
20°	1042.0
22.5°	676.6
25°	356.0
27.5°	153.2
30°	72.1
32.5°	39.0
35°	22.5
37.5°	13.6
40°	7.7
42.5°	4.1
45°	2.4
47.5°	1.8
50°	1.8
52.5°	1.8
55°	1.8
57.5°	1.8
60°	1.2
62.5°	1.2
65°	1.2
67.5°	1.2
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)