

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291631

Luminaire Tested: P3AS09R15W2N902750DE010 E3DLP1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291631  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R15W2N902750DE010 E3DLP1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 178.0 lumens  
Efficiency: N/A  
Efficacy: 19.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291631  
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291631  
 CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66		
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62		
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59		
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56		
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	76748
5°	70944
10°	56646
15°	42793
20°	32576
25°	24824
30°	17775
35°	11618
40°	7128
45°	4311
50°	2866
55°	2217
60°	1886
65°	1660
70°	1475
75°	1440
80°	1137
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4311 cd/sqm



TEST NUMBER: P1291631

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.5	16.0
10°-20°	52.7	29.6
20°-30°	46.9	26.3
30°-40°	27.8	15.6
40°-50°	11.4	6.4
50°-60°	5.3	3.0
60°-70°	3.3	1.8
70°-80°	1.7	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.1	72.0
0°-40°	155.9	87.6
0°-60°	172.6	97.0
0°-90°	178.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	178.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	350	
5°	322	29
15°	188	53
25°	103	47
35°	43	28
45°	14	11
55°	6	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1291631  
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3DLP1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	350.0
1°	349.2
2°	346.6
3°	341.4
4°	332.7
5°	322.3
6°	311.0
7°	297.7
8°	283.8
9°	269.7
10°	254.4
12.5°	219.4
15°	188.5
17.5°	161.9
20°	139.6
22.5°	120.0
25°	102.6
27.5°	85.8
30°	70.2
32.5°	56.1
35°	43.4
37.5°	33.2
40°	24.9
42.5°	18.5
45°	13.9
47.5°	10.7
50°	8.4
52.5°	6.9
55°	5.8
57.5°	4.9
60°	4.3
62.5°	3.8
65°	3.2
67.5°	2.9
70°	2.3
72.5°	2.0
75°	1.7
77.5°	1.2
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)