

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293361

Luminaire Tested: P3AS09R40W2N902765DE010 E3D1WH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902765DE010 E3D1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 740.0 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293361
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293361
 CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98		96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94		92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90		88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86		85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83		82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80		79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77		76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74		73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71		70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	377185
5°	374465
10°	364678
15°	325745
20°	215992
25°	80908
30°	21649
35°	8459
40°	3034
45°	1458
50°	443
55°	191
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1458 cd/sqm



TEST NUMBER: P1293361

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	21.7
10°-20°	380.2	51.4
20°-30°	172.4	23.3
30°-40°	22.3	3.0
40°-50°	3.9	0.5
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	713.2	96.4
0°-40°	735.5	99.4
0°-60°	739.9	100.0
0°-90°	740.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	740.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1720	
5°	1701	161
15°	1435	380
25°	334	172
35°	32	22
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1293361
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1720.1
1°	1719.1
2°	1716.5
3°	1712.6
4°	1707.7
5°	1701.2
6°	1693.7
7°	1684.4
8°	1673.0
9°	1657.5
10°	1637.8
11°	1614.7
12°	1583.9
13°	1545.8
14°	1496.1
15°	1434.9
16°	1356.9
17°	1268.1
18°	1161.4
19°	1048.7
20°	925.6
21°	802.6
22°	681.3
23°	560.6
24°	442.0
25°	334.4
26°	247.7
27°	181.3
28°	136.3
29°	106.0
30°	85.5
31°	70.7
32°	59.1
32.5°	53.9
33°	48.7
34°	39.6
35°	31.6
36°	24.9
37°	19.7
37.5°	17.6
38°	15.5
39°	13.0
40°	10.6
42.5°	7.0
45°	4.7



TEST NUMBER: P1293361
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3D1WH_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.8
50°	1.3
52.5°	0.5
55°	0.5
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)