

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291664

Luminaire Tested: P3AS09R15W2N902750DE010 E3PHLD1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRIS
Catalog Number: P3AS09R15W2N902750DE010 E3PHLD1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 390.0 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291664
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3PHLD1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1291664

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3PHLD1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113500
5°	106383
10°	87240
15°	67787
20°	53508
25°	42631
30°	34233
35°	27947
40°	23015
45°	19351
50°	16648
55°	14375
60°	12762
65°	11104
70°	9873
75°	7964
80°	6440
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19351 cd/sqm



TEST NUMBER: P1291664

CATALOG NUMBER: P3AS09R15W2N902750DE010 E3PHLD1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	11.1
10°-20°	83.6	21.4
20°-30°	81.3	20.8
30°-40°	65.7	16.8
40°-50°	48.8	12.5
50°-60°	34.1	8.7
60°-70°	21.4	5.5
70°-80°	10.1	2.6
80°-90°	1.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	208.1	53.4
0°-40°	273.8	70.2
0°-60°	356.6	91.4
0°-90°	390.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	390.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	483	43
15°	299	84
25°	176	81
35°	104	66
45°	62	49
55°	38	34
65°	21	21
75°	9	10
85°	2	2
90°	0	



TEST NUMBER: P1291664
CATALOG NUMBER: P3AS09R15W2N902750DE010 E3PHLD1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	517.6
2.5°	509.0
5°	483.3
7.5°	442.3
10°	391.8
12.5°	342.2
15°	298.6
17.5°	261.8
20°	229.3
22.5°	201.0
25°	176.2
27.5°	154.0
30°	135.2
32.5°	118.9
35°	104.4
37.5°	91.5
40°	80.4
42.5°	71.0
45°	62.4
47.5°	55.6
50°	48.8
52.5°	42.8
55°	37.6
57.5°	33.4
60°	29.1
62.5°	24.8
65°	21.4
67.5°	18.0
70°	15.4
72.5°	12.0
75°	9.4
77.5°	6.8
80°	5.1
82.5°	2.6
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)