

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293414

Luminaire Tested: P3AS09R40W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 28.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293414
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293414
 CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57912
5°	56857
10°	53595
15°	48695
20°	42774
25°	36534
30°	30258
35°	23343
40°	16603
45°	11195
50°	6106
55°	4320
60°	4035
65°	3736
70°	3334
75°	3219
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11195 cd/sqm



TEST NUMBER: P1293414

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.1	9.3
10°-20°	59.7	23.2
20°-30°	69.1	26.8
30°-40°	54.4	21.1
40°-50°	28.0	10.8
50°-60°	10.7	4.1
60°-70°	7.1	2.7
70°-80°	3.8	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	152.9	59.3
0°-40°	207.3	80.4
0°-60°	246.0	95.3
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	264	
5°	258	24
15°	214	60
25°	151	69
35°	87	54
45°	36	28
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293414
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	264.1
2.5°	262.7
5°	258.3
7.5°	250.8
10°	240.7
12.5°	228.9
15°	214.5
17.5°	199.5
20°	183.3
22.5°	166.8
25°	151.0
27.5°	135.1
30°	119.5
32.5°	103.6
35°	87.2
37.5°	71.9
40°	58.0
42.5°	46.2
45°	36.1
47.5°	26.3
50°	17.9
52.5°	13.0
55°	11.3
57.5°	10.1
60°	9.2
62.5°	8.1
65°	7.2
67.5°	6.1
70°	5.2
72.5°	4.3
75°	3.8
77.5°	2.9
80°	2.0
82.5°	1.7
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)