

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291691

Luminaire Tested: P3AS09R15W2N902765DE010 E3CD1MB\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291691  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R15W2N902765DE010 E3CD1MB\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 737.1 lumens  
Efficiency: N/A  
Efficacy: 81.9 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291691  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3CD1MB\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291691

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3CD1MB\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	97	95	98	97	95	94
4	107	103	100	97	106	102	99	97	100	97	95	98	96	94	97	95	93	97	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	95	93	92	91
6	103	98	94	92	102	97	94	92	96	93	91	95	92	91	94	92	90	94	92	90	89
7	101	96	92	90	100	95	92	90	94	91	89	93	91	89	92	90	89	92	90	89	88
8	99	94	90	88	98	93	90	88	92	90	88	92	89	87	91	89	87	91	89	87	86
9	97	92	89	87	97	92	89	86	91	88	86	90	88	86	90	87	86	90	87	86	85
10	96	90	87	85	95	90	87	85	89	87	85	89	86	85	88	86	85	88	86	85	84

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1432561
5°	1200613
10°	565543
15°	170512
20°	63099
25°	24534
30°	9141
35°	2811
40°	1002
45°	527
50°	409
55°	459
60°	526
65°	311
70°	385
75°	508
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 527 cd/sqm



TEST NUMBER: P1291691

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3CD1MB\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	421.7	57.2
10°-20°	250.7	34.0
20°-30°	52.7	7.1
30°-40°	8.5	1.2
40°-50°	1.4	0.2
50°-60°	1.1	0.1
60°-70°	0.7	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.0	98.4
0°-40°	733.5	99.5
0°-60°	736.0	99.9
0°-90°	737.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	737.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6533	
5°	5454	422
15°	751	251
25°	101	53
35°	10	8
45°	2	1
55°	1	1
65°	1	1
75°	1	0
85°	0	0
90°	0	



TEST NUMBER: P1291691  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3CD1MB\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6533.0
1°	6512.6
2°	6408.8
3°	6201.4
4°	5897.3
5°	5454.4
6°	4934.1
7°	4339.2
8°	3771.1
9°	3127.8
10°	2539.9
12.5°	1370.5
15°	751.1
17.5°	439.9
20°	270.4
22.5°	165.5
25°	101.4
27.5°	61.2
30°	36.1
32.5°	20.4
35°	10.5
37.5°	5.8
40°	3.5
42.5°	2.3
45°	1.7
47.5°	1.2
50°	1.2
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)