

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291746

Luminaire Tested: P3AS09R15W2N902765DE010 E3DL1H\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291746  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R15W2N902765DE010 E3DL1H\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 614.0 lumens  
Efficiency: N/A  
Efficacy: 68.2 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291746  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1H\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291746  
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1H\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94	93	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	90	88	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	87	86	85	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	82	81	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	80	79	78	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	77	76	75	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	74	73	72	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	72	71	70	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	68	67	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	67	66	65	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	524519
5°	465594
10°	323330
15°	191216
20°	108906
25°	62254
30°	34436
35°	18364
40°	10162
45°	5489
50°	3446
55°	2714
60°	2324
65°	2127
70°	1923
75°	2033
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5489 cd/sqm



TEST NUMBER: P1291746

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1H\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.9	29.3
10°-20°	237.4	38.7
20°-30°	122.2	19.9
30°-40°	45.9	7.5
40°-50°	15.0	2.4
50°-60°	6.5	1.1
60°-70°	4.1	0.7
70°-80°	2.5	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	539.5	87.9
0°-40°	585.4	95.3
0°-60°	606.8	98.8
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2392	
5°	2115	180
15°	842	237
25°	257	122
35°	69	46
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1291746  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1H\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2392.0
1°	2387.3
2°	2355.9
3°	2296.2
4°	2217.5
5°	2115.2
6°	1999.2
7°	1872.1
8°	1730.7
9°	1591.1
10°	1452.1
12.5°	1117.3
15°	842.3
17.5°	630.5
20°	466.7
22.5°	348.4
25°	257.3
27.5°	187.5
30°	136.0
32.5°	96.4
35°	68.6
37.5°	49.1
40°	35.5
42.5°	25.4
45°	17.7
47.5°	13.0
50°	10.1
52.5°	8.3
55°	7.1
57.5°	5.9
60°	5.3
62.5°	4.7
65°	4.1
67.5°	3.5
70°	3.0
72.5°	3.0
75°	2.4
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)