

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293501

Luminaire Tested: P3AS09R45W2N902750DE010 E3CD1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293501
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45W2N902750DE010 E3CD1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 709.0 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293501
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3CD1MMS_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1293501

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3CD1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.4	18.7
10°-20°	303.9	42.9
20°-30°	218.8	30.9
30°-40°	45.5	6.4
40°-50°	4.2	0.6
50°-60°	1.7	0.2
60°-70°	1.4	0.2
70°-80°	0.9	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.1	92.4
0°-40°	700.6	98.8
0°-60°	706.5	99.6
0°-90°	709.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1402	
5°	1404	132
15°	1106	304
25°	483	219
35°	58	46
45°	3	4
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293501
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3CD1MMS_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1401.8
2.5°	1402.3
5°	1403.9
7.5°	1393.9
10°	1345.2
12.5°	1243.7
15°	1105.7
17.5°	964.5
20°	822.3
22.5°	658.9
25°	482.8
27.5°	318.3
30°	191.9
32.5°	107.3
35°	58.2
37.5°	32.8
40°	16.9
42.5°	7.4
45°	3.2
47.5°	2.1
50°	2.1
52.5°	2.1
55°	2.1
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)