

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291792

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3DLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 417.0 lumens
Efficiency: N/A
Efficacy: 46.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291792
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291792

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1MW_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 42.9 | 10.3 |
| 10°-20° | 100.5 | 24.1 |
| 20°-30° | 110.8 | 26.6 |
| 30°-40° | 82.9 | 19.9 |
| 40°-50° | 43.0 | 10.3 |
| 50°-60° | 17.8 | 4.3 |
| 60°-70° | 11.1 | 2.7 |
| 70°-80° | 6.2 | 1.5 |
| 80°-90° | 1.8 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 254.2 | 61.0 |
| 0°-40° | 337.2 | 80.8 |
| 0°-60° | 398.0 | 95.4 |
| 0°-90° | 417.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 417.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 480 | |
| 5° | 465 | 43 |
| 15° | 361 | 101 |
| 25° | 242 | 111 |
| 35° | 132 | 83 |
| 45° | 54 | 43 |
| 55° | 18 | 18 |
| 65° | 11 | 11 |
| 75° | 6 | 6 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P1291792
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 479.7 |
| 1° | 480.2 |
| 2° | 478.6 |
| 3° | 475.4 |
| 4° | 470.7 |
| 5° | 464.9 |
| 6° | 457.5 |
| 7° | 449.6 |
| 8° | 440.1 |
| 9° | 430.0 |
| 10° | 420.0 |
| 12.5° | 390.9 |
| 15° | 360.8 |
| 17.5° | 330.7 |
| 20° | 301.1 |
| 22.5° | 271.0 |
| 25° | 242.5 |
| 27.5° | 214.0 |
| 30° | 185.4 |
| 32.5° | 157.4 |
| 35° | 131.5 |
| 37.5° | 109.4 |
| 40° | 89.3 |
| 42.5° | 70.8 |
| 45° | 53.9 |
| 47.5° | 40.7 |
| 50° | 30.6 |
| 52.5° | 22.7 |
| 55° | 18.5 |
| 57.5° | 16.4 |
| 60° | 14.3 |
| 62.5° | 12.7 |
| 65° | 11.1 |
| 67.5° | 9.5 |
| 70° | 8.5 |
| 72.5° | 6.9 |
| 75° | 5.8 |
| 77.5° | 4.8 |
| 80° | 3.7 |
| 82.5° | 2.6 |
| 85° | 1.6 |
| 87.5° | 0.5 |
| 90° | 0.0 |

(END OF REPORT)