

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291810

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 160.0 lumens
Efficiency: N/A
Efficacy: 17.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291810
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291810
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68986
5°	63768
10°	50901
15°	38457
20°	29286
25°	22308
30°	15977
35°	10440
40°	6383
45°	3876
50°	2559
55°	1988
60°	1710
65°	1505
70°	1346
75°	1356
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3876 cd/sqm



TEST NUMBER: P1291810
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	16.0
10°-20°	47.3	29.6
20°-30°	42.1	26.3
30°-40°	24.9	15.6
40°-50°	10.2	6.4
50°-60°	4.8	3.0
60°-70°	2.9	1.8
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.2	72.0
0°-40°	140.1	87.6
0°-60°	155.1	96.9
0°-90°	160.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	160.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	315	
5°	290	26
15°	169	47
25°	92	42
35°	39	25
45°	12	10
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1291810
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	314.6
1°	313.9
2°	311.5
3°	306.9
4°	299.1
5°	289.7
6°	279.6
7°	267.6
8°	255.1
9°	242.4
10°	228.6
12.5°	197.2
15°	169.4
17.5°	145.5
20°	125.5
22.5°	107.8
25°	92.2
27.5°	77.2
30°	63.1
32.5°	50.4
35°	39.0
37.5°	29.9
40°	22.3
42.5°	16.6
45°	12.5
47.5°	9.6
50°	7.5
52.5°	6.2
55°	5.2
57.5°	4.4
60°	3.9
62.5°	3.4
65°	2.9
67.5°	2.6
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.0
80°	0.8
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)