

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291834

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLP1WH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291834  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R15W2N902765DE010 E3DLP1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 549.0 lumens  
Efficiency: N/A  
Efficacy: 61.0 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291834  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1WH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291834  
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	468998
5°	416310
10°	289106
15°	170966
20°	97378
25°	55673
30°	30790
35°	16410
40°	9074
45°	4931
50°	3070
55°	2409
60°	2105
65°	1920
70°	1667
75°	1779
80°	1389
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4931 cd/sqm



TEST NUMBER: P1291834

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1WH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.8	29.3
10°-20°	212.3	38.7
20°-30°	109.3	19.9
30°-40°	41.0	7.5
40°-50°	13.4	2.4
50°-60°	5.8	1.1
60°-70°	3.7	0.7
70°-80°	2.1	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	482.4	87.9
0°-40°	523.4	95.3
0°-60°	542.6	98.8
0°-90°	549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2139	
5°	1891	161
15°	753	212
25°	230	109
35°	61	41
45°	16	13
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1291834  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLP1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2138.8
1°	2134.5
2°	2106.5
3°	2053.1
4°	1982.7
5°	1891.3
6°	1787.6
7°	1673.9
8°	1547.5
9°	1422.7
10°	1298.4
12.5°	999.0
15°	753.1
17.5°	563.8
20°	417.3
22.5°	311.5
25°	230.1
27.5°	167.7
30°	121.6
32.5°	86.2
35°	61.3
37.5°	43.9
40°	31.7
42.5°	22.7
45°	15.9
47.5°	11.6
50°	9.0
52.5°	7.4
55°	6.3
57.5°	5.3
60°	4.8
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)