

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293586

Luminaire Tested: P3AS09R45W2N902750DE010 E3DLP1LI\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293586  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902750DE010 E3DLP1LI\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 381.0 lumens  
Efficiency: N/A  
Efficacy: 42.3 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293586  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLP1LI\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293586

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLP1LI\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113478
5°	110896
10°	102292
15°	88945
20°	73086
25°	56858
30°	41981
35°	29553
40°	18435
45°	9986
50°	5390
55°	4626
60°	4166
65°	3580
70°	3077
75°	3135
80°	2652
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9986 cd/sqm



TEST NUMBER: P1293586

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLP1LI\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.7	12.2
10°-20°	108.3	28.4
20°-30°	107.5	28.2
30°-40°	69.3	18.2
40°-50°	26.7	7.0
50°-60°	10.8	2.8
60°-70°	6.9	1.8
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	262.5	68.9
0°-40°	331.8	87.1
0°-60°	369.3	96.9
0°-90°	381.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	381.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	518	
5°	504	47
15°	392	108
25°	235	108
35°	110	69
45°	32	27
55°	12	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293586  
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DLP1LI\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	517.5
2.5°	514.9
5°	503.8
7.5°	484.8
10°	459.4
12.5°	427.8
15°	391.8
17.5°	352.8
20°	313.2
22.5°	273.0
25°	235.0
27.5°	199.1
30°	165.8
32.5°	136.8
35°	110.4
37.5°	86.6
40°	64.4
42.5°	46.5
45°	32.2
47.5°	21.7
50°	15.8
52.5°	13.2
55°	12.1
57.5°	10.6
60°	9.5
62.5°	7.9
65°	6.9
67.5°	5.8
70°	4.8
72.5°	4.2
75°	3.7
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)