

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291919

Luminaire Tested: P3AS09R20W2N902750DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20W2N902750DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 268.0 lumens
Efficiency: N/A
Efficacy: 29.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291919
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291919

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206190
5°	187431
10°	138519
15°	85699
20°	48934
25°	27945
30°	15673
35°	8513
40°	4666
45°	2574
50°	1501
55°	1070
60°	1009
65°	934
70°	833
75°	847
80°	631
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2574 cd/sqm



TEST NUMBER: P1291919

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.7	27.5
10°-20°	105.3	39.3
20°-30°	54.9	20.5
30°-40°	21.2	7.9
40°-50°	6.9	2.6
50°-60°	2.7	1.0
60°-70°	1.8	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.0	87.3
0°-40°	255.2	95.2
0°-60°	264.8	98.8
0°-90°	268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	940	
5°	852	74
15°	378	105
25°	116	55
35°	32	21
45°	8	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1291919
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	940.3
1°	938.5
2°	927.4
3°	910.3
4°	883.9
5°	851.5
6°	813.2
7°	770.7
8°	721.6
9°	673.7
10°	622.1
12.5°	494.5
15°	377.5
17.5°	282.5
20°	209.7
22.5°	155.3
25°	115.5
27.5°	85.2
30°	61.9
32.5°	44.8
35°	31.8
37.5°	23.0
40°	16.3
42.5°	11.7
45°	8.3
47.5°	6.0
50°	4.4
52.5°	3.4
55°	2.8
57.5°	2.6
60°	2.3
62.5°	2.1
65°	1.8
67.5°	1.6
70°	1.3
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)