

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293722

Luminaire Tested: P3AS09R45W2N902765DE010 E3DLP1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293722  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R45W2N902765DE010 E3DLP1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 209.0 lumens  
Efficiency: N/A  
Efficacy: 23.2 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293722  
CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1GPH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293722  
 CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1GPH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86	86	86	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79	79	79	79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74	74	74	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69	69	69	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64	64	64	64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60	60	60	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56	56	56	56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	53	53	53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50	50	50	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62254
5°	60841
10°	56111
15°	48786
20°	40090
25°	31187
30°	23042
35°	16195
40°	10105
45°	5489
50°	2968
55°	2561
60°	2281
65°	1972
70°	1667
75°	1694
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5489 cd/sqm



TEST NUMBER: P1293722

CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	25.6	12.2
10°-20°	59.4	28.4
20°-30°	59.0	28.2
30°-40°	38.0	18.2
40°-50°	14.6	7.0
50°-60°	5.9	2.8
60°-70°	3.8	1.8
70°-80°	2.0	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.0	68.9
0°-40°	182.0	87.1
0°-60°	202.6	96.9
0°-90°	209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	209.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	284	
5°	276	26
15°	215	59
25°	129	59
35°	60	38
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1293722  
CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	283.9
2.5°	282.4
5°	276.4
7.5°	265.9
10°	252.0
12.5°	234.6
15°	214.9
17.5°	193.5
20°	171.8
22.5°	149.8
25°	128.9
27.5°	109.2
30°	91.0
32.5°	75.0
35°	60.5
37.5°	47.5
40°	35.3
42.5°	25.5
45°	17.7
47.5°	11.9
50°	8.7
52.5°	7.2
55°	6.7
57.5°	5.8
60°	5.2
62.5°	4.3
65°	3.8
67.5°	3.2
70°	2.6
72.5°	2.3
75°	2.0
77.5°	1.4
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)