

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292093

Luminaire Tested: P3AS09R20W2N902765DE010 E3DLD1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292093  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R20W2N902765DE010 E3DLD1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 4000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 228.0 lumens  
Efficiency: N/A  
Efficacy: 25.3 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292093  
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1GPH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292093

CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	56399
5°	54898
10°	50500
15°	44450
20°	38107
25°	32034
30°	25877
35°	19702
40°	13998
45°	9241
50°	5731
55°	3747
60°	3421
65°	3165
70°	2949
75°	2711
80°	2526
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9241 cd/sqm



TEST NUMBER: P1292093

CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1GPH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.1	10.1
10°-20°	54.5	23.9
20°-30°	60.5	26.5
30°-40°	46.2	20.2
40°-50°	23.6	10.4
50°-60°	9.7	4.3
60°-70°	6.1	2.7
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	138.1	60.6
0°-40°	184.2	80.8
0°-60°	217.6	95.4
0°-90°	228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	228.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	257	
5°	249	23
15°	196	55
25°	132	60
35°	74	46
45°	30	24
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292093  
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	257.2
1°	257.5
2°	256.3
3°	254.9
4°	252.6
5°	249.4
6°	245.6
7°	241.5
8°	237.2
9°	232.0
10°	226.8
12.5°	211.7
15°	195.8
17.5°	179.6
20°	163.3
22.5°	147.1
25°	132.4
27.5°	117.6
30°	102.2
32.5°	87.8
35°	73.6
37.5°	61.1
40°	48.9
42.5°	38.5
45°	29.8
47.5°	22.6
50°	16.8
52.5°	12.5
55°	9.8
57.5°	9.0
60°	7.8
62.5°	7.0
65°	6.1
67.5°	5.2
70°	4.6
72.5°	3.8
75°	3.2
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.3
90°	0.0

(END OF REPORT)