

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293841

Luminaire Tested: P3AS09R50W2N902750DE010 E3DLD1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293841  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50W2N902750DE010 E3DLD1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 227.0 lumens  
Efficiency: N/A  
Efficacy: 25.2 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293841  
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293841

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83				83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75				75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69				69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58				58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53				53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50				50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46				46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43				43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	46137
5°	45454
10°	43442
15°	40227
20°	36146
25°	31792
30°	27017
35°	21924
40°	16459
45°	10606
50°	5049
55°	3976
60°	3728
65°	3476
70°	3142
75°	2881
80°	2652
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10606 cd/sqm



TEST NUMBER: P1293841  
 CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	19.4	8.5
10°-20°	49.4	21.8
20°-30°	60.0	26.4
30°-40°	50.9	22.4
40°-50°	26.5	11.7
50°-60°	9.5	4.2
60°-70°	6.6	2.9
70°-80°	3.6	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	128.8	56.7
0°-40°	179.7	79.2
0°-60°	215.7	95.0
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	210	
5°	206	19
15°	177	49
25°	131	60
35°	82	51
45°	34	26
55°	10	10
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1293841  
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	210.4
2.5°	209.6
5°	206.5
7.5°	201.8
10°	195.1
12.5°	186.5
15°	177.2
17.5°	166.6
20°	154.9
22.5°	143.0
25°	131.4
27.5°	119.2
30°	106.7
32.5°	94.3
35°	81.9
37.5°	69.7
40°	57.5
42.5°	45.9
45°	34.2
47.5°	22.8
50°	14.8
52.5°	11.4
55°	10.4
57.5°	9.3
60°	8.5
62.5°	7.5
65°	6.7
67.5°	5.7
70°	4.9
72.5°	4.1
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)