

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292236

Luminaire Tested: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 229.0 lumens
Efficiency: N/A
Efficacy: 25.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292236
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292236
 CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54425
5°	53137
10°	49231
15°	43837
20°	37687
25°	32034
30°	26358
35°	20532
40°	14771
45°	9365
50°	5561
55°	3823
60°	3508
65°	3269
70°	2949
75°	2626
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9365 cd/sqm



TEST NUMBER: P1292236

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.4	9.8
10°-20°	53.6	23.4
20°-30°	60.6	26.5
30°-40°	47.9	20.9
40°-50°	24.2	10.6
50°-60°	9.7	4.2
60°-70°	6.2	2.7
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	136.6	59.6
0°-40°	184.5	80.6
0°-60°	218.4	95.4
0°-90°	229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	229.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	248	
5°	241	22
15°	193	54
25°	132	61
35°	77	48
45°	30	24
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292236
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	248.2
1°	248.2
2°	247.3
3°	245.9
4°	243.9
5°	241.4
6°	238.2
7°	234.5
8°	230.5
9°	225.9
10°	221.1
11°	215.7
12°	210.5
13°	204.5
14°	198.8
15°	193.1
17.5°	177.2
20°	161.5
22.5°	146.6
25°	132.4
27.5°	118.4
30°	104.1
32.5°	90.7
35°	76.7
37.5°	63.9
40°	51.6
42.5°	40.2
45°	30.2
47.5°	22.5
50°	16.3
52.5°	12.3
55°	10.0
57.5°	9.1
60°	8.0
62.5°	7.1
65°	6.3
67.5°	5.4
70°	4.6
72.5°	4.0
75°	3.1
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.3



TEST NUMBER: P1292236
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)