

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292258

Luminaire Tested: P3AS09R25W2N902750DE010 E3DLD1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902750DE010 E3DLD1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 52.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292258
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292258
 CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.4	9.8
10°-20°	111.2	23.4
20°-30°	125.7	26.5
30°-40°	99.4	20.9
40°-50°	50.2	10.6
50°-60°	20.1	4.2
60°-70°	12.9	2.7
70°-80°	7.1	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.3	59.6
0°-40°	382.7	80.6
0°-60°	453.0	95.4
0°-90°	475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	515	
5°	501	46
15°	401	111
25°	275	126
35°	159	99
45°	63	50
55°	21	20
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1292258
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1WH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	514.8
1°	514.8
2°	513.0
3°	510.1
4°	505.9
5°	500.6
6°	494.1
7°	486.4
8°	478.1
9°	468.7
10°	458.6
11°	447.4
12°	436.7
13°	424.3
14°	412.4
15°	400.6
17.5°	367.5
20°	334.9
22.5°	304.2
25°	274.6
27.5°	245.6
30°	216.0
32.5°	188.2
35°	159.2
37.5°	132.6
40°	107.1
42.5°	83.4
45°	62.7
47.5°	46.7
50°	33.7
52.5°	25.4
55°	20.7
57.5°	18.9
60°	16.6
62.5°	14.8
65°	13.0
67.5°	11.2
70°	9.5
72.5°	8.3
75°	6.5
77.5°	5.3
80°	4.1
82.5°	3.0
85°	1.8
87.5°	0.6



TEST NUMBER: P1292258
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1WH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)