

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293854

Luminaire Tested: P3AS09R50W2N902750DE010 E3DLD1LI\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293854  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50W2N902750DE010 E3DLD1LI\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 517.9 lumens  
Efficiency: N/A  
Efficacy: 57.5 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293854  
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1LI\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293854

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1LI\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	105277
5°	103720
10°	99130
15°	91805
20°	82491
25°	72512
30°	61680
35°	50005
40°	37556
45°	24189
50°	11496
55°	9022
60°	8552
65°	7990
70°	7181
75°	6524
80°	5935
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24189 cd/sqm



TEST NUMBER: P1293854

CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1LI\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.2	8.5
10°-20°	112.7	21.8
20°-30°	137.0	26.4
30°-40°	116.2	22.4
40°-50°	60.3	11.6
50°-60°	21.8	4.2
60°-70°	15.0	2.9
70°-80°	8.2	1.6
80°-90°	2.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	293.9	56.7
0°-40°	410.0	79.2
0°-60°	492.1	95.0
0°-90°	517.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	517.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	480	
5°	471	44
15°	404	113
25°	300	137
35°	187	116
45°	78	60
55°	24	22
65°	15	15
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1293854  
CATALOG NUMBER: P3AS09R50W2N902750DE010 E3DLD1LI\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	480.1
2.5°	478.3
5°	471.2
7.5°	460.5
10°	445.2
12.5°	425.7
15°	404.4
17.5°	380.1
20°	353.5
22.5°	326.3
25°	299.7
27.5°	272.0
30°	243.6
32.5°	215.2
35°	186.8
37.5°	159.0
40°	131.2
42.5°	104.6
45°	78.0
47.5°	52.0
50°	33.7
52.5°	26.0
55°	23.6
57.5°	21.3
60°	19.5
62.5°	17.1
65°	15.4
67.5°	13.0
70°	11.2
72.5°	9.5
75°	7.7
77.5°	5.9
80°	4.7
82.5°	3.5
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)