

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293925

Luminaire Tested: P3AS09R50W2N902765DE010 E3CD1MMS\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293925  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50W2N902765DE010 E3CD1MMS\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,  
E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 723.0 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293925  
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3CD1MMS\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293925

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3CD1MMS\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	251800
5°	247303
10°	237448
15°	217731
20°	192003
25°	147154
30°	80012
35°	25752
40°	6040
45°	806
50°	716
55°	803
60°	702
65°	830
70°	705
75°	932
80°	631
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 85°  
 Luminance: 1258 cd/sqm



TEST NUMBER: P1293925

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3CD1MMS\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.4	14.6
10°-20°	266.6	36.9
20°-30°	267.0	36.9
30°-40°	75.1	10.4
40°-50°	4.5	0.6
50°-60°	1.7	0.2
60°-70°	1.4	0.2
70°-80°	0.9	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.0	88.4
0°-40°	714.1	98.8
0°-60°	720.3	99.6
0°-90°	723.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	723.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1148	
5°	1124	105
15°	959	267
25°	608	267
35°	96	75
45°	3	5
55°	2	2
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293925  
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3CD1MMS\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1148.3
2.5°	1142.5
5°	1123.5
7.5°	1097.6
10°	1066.4
12.5°	1019.4
15°	959.1
17.5°	889.9
20°	822.8
22.5°	739.3
25°	608.2
27.5°	452.9
30°	316.0
32.5°	190.8
35°	96.2
37.5°	45.4
40°	21.1
42.5°	7.9
45°	2.6
47.5°	2.1
50°	2.1
52.5°	2.1
55°	2.1
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)