

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292295

Luminaire Tested: P3AS09R25W2N902750DE010 E3PH1MW\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292295  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902750DE010 E3PH1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,  
E3PH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 562.0 lumens  
Efficiency: N/A  
Efficacy: 62.4 lumens/watt  
Spacing Criteria (0/90/45): 0.36 / 0.36 / 0.36  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292295  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PH1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292295  
 CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PH1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100	
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	99	99	98	98	98	98
2	113	109	107	105	111	108	105	103	105	103	101	102	100	99	99	98	97	99	98	97	96	
3	110	106	103	100	108	104	102	99	102	100	98	100	98	96	98	96	95	98	96	95	94	
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92	
5	105	100	96	94	103	99	96	93	97	95	93	96	94	92	95	93	91	95	93	91	90	
6	102	97	94	91	101	97	93	91	95	93	91	94	92	90	93	91	89	93	91	89	89	
7	100	95	92	89	99	95	91	89	94	91	89	93	90	88	92	89	88	92	89	88	87	
8	98	93	90	87	98	93	89	87	92	89	87	91	88	87	90	88	86	90	88	86	85	
9	97	91	88	86	96	91	88	85	90	87	85	89	87	85	89	86	85	89	86	85	84	
10	95	89	86	84	94	89	86	84	88	86	84	88	85	83	87	85	83	87	85	83	83	

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	859558
5°	734117
10°	462828
15°	215416
20°	44361
25°	9049
30°	1924
35°	402
40°	229
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1292295

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PH1MW\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	277.9	49.5
10°-20°	258.1	45.9
20°-30°	24.4	4.3
30°-40°	1.4	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	560.5	99.7
0°-40°	561.9	100.0
0°-60°	562.0	100.0
0°-90°	562.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	562.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3920	
5°	3335	278
15°	949	258
25°	37	24
35°	2	1
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1292295  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PH1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3919.9
2.5°	3774.1
5°	3335.1
7.5°	2742.0
10°	2078.6
12.5°	1501.5
15°	948.9
17.5°	458.8
20°	190.1
22.5°	75.6
25°	37.4
27.5°	17.6
30°	7.6
32.5°	3.1
35°	1.5
37.5°	0.8
40°	0.8
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)