

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293937

Luminaire Tested: P3AS09R50W2N902765DE010 E3D1H\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293937  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R50W2N902765DE010 E3D1H\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 734.0 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293937  
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1H\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1293937

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1H\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.2	14.5
10°-20°	263.3	35.9
20°-30°	276.7	37.7
30°-40°	79.2	10.8
40°-50°	7.7	1.1
50°-60°	0.6	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.2	88.0
0°-40°	725.4	98.8
0°-60°	733.8	100.0
0°-90°	734.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1170	
5°	1134	106
15°	950	263
25°	633	277
35°	102	79
45°	8	8
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1293937

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1H\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1169.8
1°	1167.9
2°	1162.8
3°	1155.2
4°	1145.1
5°	1134.3
6°	1122.6
7°	1110.2
8°	1098.5
9°	1085.1
10°	1070.0
11°	1052.7
12°	1032.8
13°	1007.9
14°	981.0
15°	950.1
16°	917.5
17°	885.9
18°	853.6
19°	825.1
20°	799.7
21°	775.3
22°	747.6
23°	715.8
24°	678.5
25°	632.7
26°	582.9
27°	527.5
28°	472.4
29°	412.8
30°	347.3
31°	285.9
32°	229.4
32.5°	204.8
33°	180.0
34°	138.0
35°	102.0
36°	74.8
37°	55.7
37.5°	48.2
38°	41.7
39°	32.4
40°	25.6
42.5°	14.5
45°	8.3



TEST NUMBER: P1293937

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3D1H\_2700K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	4.7
50°	1.8
52.5°	0.8
55°	0.5
57.5°	0.5
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)