

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292302

Luminaire Tested: P3AS09R25W2N902750DE010 E3PHLD1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902750DE010 E3PHLD1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 52.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292302
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1292302

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123937
5°	117653
10°	101891
15°	82952
20°	65549
25°	52261
30°	42361
35°	34506
40°	28596
45°	24096
50°	20400
55°	17968
60°	15744
65°	13750
70°	12053
75°	10167
80°	7577
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 24096 cd/sqm



TEST NUMBER: P1292302

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	10.2
10°-20°	101.3	21.3
20°-30°	99.9	21.0
30°-40°	81.3	17.1
40°-50°	60.3	12.7
50°-60°	42.1	8.9
60°-70°	26.4	5.6
70°-80°	12.7	2.7
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.7	52.6
0°-40°	331.0	69.7
0°-60°	433.5	91.3
0°-90°	475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	565	
5°	534	49
15°	365	101
25°	216	100
35°	129	81
45°	78	60
55°	47	42
65°	26	26
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P1292302
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	565.2
2.5°	557.5
5°	534.5
7.5°	499.5
10°	457.6
12.5°	411.5
15°	365.4
17.5°	320.2
20°	280.9
22.5°	246.7
25°	216.0
27.5°	189.5
30°	167.3
32.5°	146.8
35°	128.9
37.5°	113.6
40°	99.9
42.5°	87.9
45°	77.7
47.5°	68.3
50°	59.8
52.5°	52.9
55°	47.0
57.5°	41.0
60°	35.9
62.5°	30.7
65°	26.5
67.5°	22.2
70°	18.8
72.5°	15.4
75°	12.0
77.5°	8.5
80°	6.0
82.5°	3.4
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)