

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292379

Luminaire Tested: P3AS09R25W2N902765DE010 E3DL1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902765DE010 E3DL1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 304.0 lumens
Efficiency: N/A
Efficacy: 33.8 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292379
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292379

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	82	78	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	79	75	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	76	73	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	73	70	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	71	67	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195006
5°	181928
10°	145733
15°	98934
20°	59855
25°	35010
30°	19927
35°	10975
40°	5811
45°	3070
50°	1774
55°	1338
60°	1140
65°	1193
70°	1090
75°	1017
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3070 cd/sqm



TEST NUMBER: P1292379

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.3	24.1
10°-20°	119.8	39.4
20°-30°	68.5	22.5
30°-40°	27.0	8.9
40°-50°	8.3	2.7
50°-60°	3.3	1.1
60°-70°	2.2	0.7
70°-80°	1.3	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.6	86.1
0°-40°	288.6	94.9
0°-60°	300.2	98.7
0°-90°	304.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	304.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	889	
5°	826	73
15°	436	120
25°	145	68
35°	41	27
45°	10	8
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1292379
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	889.3
1°	887.5
2°	880.3
3°	867.5
4°	849.8
5°	826.5
6°	799.2
7°	768.4
8°	732.7
9°	696.1
10°	654.5
11°	613.6
12°	568.6
13°	524.1
14°	478.5
15°	435.8
17.5°	337.9
20°	256.5
22.5°	192.6
25°	144.7
27.5°	107.2
30°	78.7
32.5°	56.9
35°	41.0
37.5°	29.1
40°	20.3
42.5°	13.9
45°	9.9
47.5°	7.0
50°	5.2
52.5°	4.1
55°	3.5
57.5°	3.2
60°	2.6
62.5°	2.3
65°	2.3
67.5°	2.0
70°	1.7
72.5°	1.5
75°	1.2
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.3



TEST NUMBER: P1292379
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1GPH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)