

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294228

Luminaire Tested: P3AS09R55W2N902765DE010 E3CB1MMS\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294228  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R55W2N902765DE010 E3CB1MMS\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,  
E3CB1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 787.0 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294228  
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CB1MMS\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294228

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CB1MMS\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |   |
| 2   | 109 | 104 | 101 | 98  | 107 | 103 | 99  | 96  | 100 | 97  | 94  | 97  | 94  | 92  | 94  | 92  | 90  | 89  |    |    |   |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 89  | 94  | 91  | 88  | 92  | 89  | 86  | 90  | 87  | 85  | 84  |    |    |   |
| 4   | 99  | 92  | 87  | 84  | 98  | 91  | 87  | 83  | 89  | 85  | 82  | 87  | 84  | 81  | 85  | 83  | 80  | 79  |    |    |   |
| 5   | 95  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  | 83  | 79  | 76  | 82  | 78  | 76  | 74  |    |    |   |
| 6   | 91  | 83  | 77  | 73  | 89  | 82  | 77  | 73  | 80  | 76  | 72  | 79  | 75  | 72  | 78  | 74  | 72  | 70  |    |    |   |
| 7   | 87  | 78  | 73  | 69  | 85  | 78  | 72  | 69  | 76  | 72  | 68  | 75  | 71  | 68  | 74  | 70  | 68  | 66  |    |    |   |
| 8   | 83  | 74  | 69  | 65  | 82  | 74  | 68  | 65  | 73  | 68  | 65  | 72  | 67  | 64  | 71  | 67  | 64  | 63  |    |    |   |
| 9   | 79  | 71  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 61  | 68  | 64  | 61  | 60  |    |    |   |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 58  | 65  | 61  | 58  | 57  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 218272 |
| 5°  | 216244 |
| 10° | 224935 |
| 15° | 221817 |
| 20° | 204534 |
| 25° | 166437 |
| 30° | 101079 |
| 35° | 34987  |
| 40° | 9990   |
| 45° | 4776   |
| 50° | 2013   |
| 55° | 918    |
| 60° | 1053   |
| 65° | 934    |
| 70° | 769    |
| 75° | 1017   |
| 80° | 758    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4776 cd/sqm



TEST NUMBER: P1294228

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CB1MMS\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 95.0   | 12.1      |
| 10°-20°   | 271.6  | 34.5      |
| 20°-30°   | 302.7  | 38.5      |
| 30°-40°   | 99.0   | 12.6      |
| 40°-50°   | 13.1   | 1.7       |
| 50°-60°   | 2.8    | 0.4       |
| 60°-70°   | 1.6    | 0.2       |
| 70°-80°   | 1.0    | 0.1       |
| 80°-90°   | 0.2    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 669.3  | 85.0      |
| 0°-40°    | 768.3  | 97.6      |
| 0°-60°    | 784.1  | 99.6      |
| 0°-90°    | 787.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 787.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 995 |      |
| 5°  | 982 | 95   |
| 15° | 977 | 272  |
| 25° | 688 | 303  |
| 35° | 131 | 99   |
| 45° | 15  | 13   |
| 55° | 2   | 3    |
| 65° | 2   | 2    |
| 75° | 1   | 1    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1294228  
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CB1MMS\_3500K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 995.4  |
| 2.5°  | 988.3  |
| 5°    | 982.4  |
| 7.5°  | 996.6  |
| 10°   | 1010.2 |
| 12.5° | 1003.1 |
| 15°   | 977.1  |
| 17.5° | 935.7  |
| 20°   | 876.5  |
| 22.5° | 794.9  |
| 25°   | 687.9  |
| 27.5° | 551.8  |
| 30°   | 399.2  |
| 32.5° | 244.9  |
| 35°   | 130.7  |
| 37.5° | 66.2   |
| 40°   | 34.9   |
| 42.5° | 22.5   |
| 45°   | 15.4   |
| 47.5° | 10.6   |
| 50°   | 5.9    |
| 52.5° | 3.5    |
| 55°   | 2.4    |
| 57.5° | 2.4    |
| 60°   | 2.4    |
| 62.5° | 1.8    |
| 65°   | 1.8    |
| 67.5° | 1.2    |
| 70°   | 1.2    |
| 72.5° | 1.2    |
| 75°   | 1.2    |
| 77.5° | 0.6    |
| 80°   | 0.6    |
| 82.5° | 0.6    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)