

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292449

Luminaire Tested: P3AS09R25W2N902765DE010 E3DLP1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292449  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902765DE010 E3DLP1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 183.0 lumens  
Efficiency: N/A  
Efficacy: 20.3 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292449  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1292449

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.4	14.4
10°-20°	54.7	29.9
20°-30°	49.4	27.0
30°-40°	29.7	16.2
40°-50°	11.8	6.4
50°-60°	5.4	3.0
60°-70°	3.3	1.8
70°-80°	1.8	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	130.5	71.3
0°-40°	160.2	87.5
0°-60°	177.4	96.9
0°-90°	183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	183.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	303	
5°	290	26
15°	198	55
25°	108	49
35°	47	30
45°	14	12
55°	6	5
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1292449  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	303.0
1°	303.0
2°	301.6
3°	298.4
4°	294.4
5°	289.6
6°	283.3
7°	276.2
8°	267.9
9°	259.6
10°	250.8
11°	240.5
12°	230.0
13°	219.4
14°	208.8
15°	197.7
17.5°	171.5
20°	147.8
22.5°	126.4
25°	107.8
27.5°	90.4
30°	74.5
32.5°	59.9
35°	46.8
37.5°	35.7
40°	26.5
42.5°	19.4
45°	14.3
47.5°	10.8
50°	8.3
52.5°	6.8
55°	6.0
57.5°	5.1
60°	4.6
62.5°	3.7
65°	3.4
67.5°	2.9
70°	2.3
72.5°	2.0
75°	1.7
77.5°	1.4
80°	0.9
82.5°	0.6
85°	0.6
87.5°	0.3



TEST NUMBER: P1292449  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH\_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)