

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294242

Luminaire Tested: P3AS09R55W2N902765DE010 E3CD1MB_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294242
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902765DE010 E3CD1MB_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 783.1 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294242
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MB_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294242

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.5	12.1
10°-20°	270.2	34.5
20°-30°	301.2	38.5
30°-40°	98.5	12.6
40°-50°	13.0	1.7
50°-60°	2.8	0.4
60°-70°	1.6	0.2
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	665.9	85.0
0°-40°	764.4	97.6
0°-60°	780.2	99.6
0°-90°	783.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	783.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	990	
5°	977	94
15°	972	270
25°	684	301
35°	130	99
45°	15	13
55°	2	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1294242
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MB_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	990.4
2.5°	983.3
5°	977.4
7.5°	991.5
10°	1005.1
12.5°	998.0
15°	972.1
17.5°	930.9
20°	872.1
22.5°	790.9
25°	684.4
27.5°	549.0
30°	397.2
32.5°	243.6
35°	130.0
37.5°	65.9
40°	34.7
42.5°	22.4
45°	15.3
47.5°	10.6
50°	5.9
52.5°	3.5
55°	2.4
57.5°	2.4
60°	2.4
62.5°	1.8
65°	1.8
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)