

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294248

Luminaire Tested: P3AS09R55W2N902765DE010 E3CD1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902765DE010 E3CD1MMS_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 783.1 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294248
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MMS_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294248
 CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | |
| 2 | 109 | 104 | 101 | 98 | 107 | 103 | 99 | 96 | 100 | 97 | 94 | 97 | 94 | 92 | 94 | 92 | 90 | 89 | | |
| 3 | 104 | 98 | 94 | 90 | 102 | 97 | 93 | 89 | 94 | 91 | 88 | 92 | 89 | 86 | 90 | 87 | 85 | 84 | | |
| 4 | 99 | 92 | 87 | 84 | 98 | 91 | 87 | 83 | 89 | 85 | 82 | 87 | 84 | 81 | 85 | 83 | 80 | 79 | | |
| 5 | 95 | 87 | 82 | 78 | 93 | 86 | 81 | 78 | 85 | 80 | 77 | 83 | 79 | 76 | 82 | 78 | 76 | 74 | | |
| 6 | 91 | 83 | 77 | 73 | 89 | 82 | 77 | 73 | 80 | 76 | 72 | 79 | 75 | 72 | 78 | 74 | 72 | 70 | | |
| 7 | 87 | 78 | 73 | 69 | 85 | 78 | 72 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 66 | | |
| 8 | 83 | 74 | 69 | 65 | 82 | 74 | 68 | 65 | 73 | 68 | 65 | 72 | 67 | 64 | 71 | 67 | 64 | 63 | | |
| 9 | 79 | 71 | 65 | 61 | 78 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 68 | 64 | 61 | 60 | | |
| 10 | 76 | 67 | 62 | 58 | 75 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 65 | 61 | 58 | 57 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 217176 |
| 5° | 215144 |
| 10° | 223799 |
| 15° | 220682 |
| 20° | 203508 |
| 25° | 165590 |
| 30° | 100572 |
| 35° | 34800 |
| 40° | 9933 |
| 45° | 4745 |
| 50° | 2013 |
| 55° | 918 |
| 60° | 1053 |
| 65° | 934 |
| 70° | 769 |
| 75° | 1017 |
| 80° | 758 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4745 cd/sqm



TEST NUMBER: P1294248

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MMS_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 94.5 | 12.1 |
| 10°-20° | 270.2 | 34.5 |
| 20°-30° | 301.2 | 38.5 |
| 30°-40° | 98.5 | 12.6 |
| 40°-50° | 13.0 | 1.7 |
| 50°-60° | 2.8 | 0.4 |
| 60°-70° | 1.6 | 0.2 |
| 70°-80° | 1.0 | 0.1 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 665.9 | 85.0 |
| 0°-40° | 764.4 | 97.6 |
| 0°-60° | 780.2 | 99.6 |
| 0°-90° | 783.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 783.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 990 | |
| 5° | 977 | 94 |
| 15° | 972 | 270 |
| 25° | 684 | 301 |
| 35° | 130 | 99 |
| 45° | 15 | 13 |
| 55° | 2 | 3 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1294248
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 990.4 |
| 2.5° | 983.3 |
| 5° | 977.4 |
| 7.5° | 991.5 |
| 10° | 1005.1 |
| 12.5° | 998.0 |
| 15° | 972.1 |
| 17.5° | 930.9 |
| 20° | 872.1 |
| 22.5° | 790.9 |
| 25° | 684.4 |
| 27.5° | 549.0 |
| 30° | 397.2 |
| 32.5° | 243.6 |
| 35° | 130.0 |
| 37.5° | 65.9 |
| 40° | 34.7 |
| 42.5° | 22.4 |
| 45° | 15.3 |
| 47.5° | 10.6 |
| 50° | 5.9 |
| 52.5° | 3.5 |
| 55° | 2.4 |
| 57.5° | 2.4 |
| 60° | 2.4 |
| 62.5° | 1.8 |
| 65° | 1.8 |
| 67.5° | 1.2 |
| 70° | 1.2 |
| 72.5° | 1.2 |
| 75° | 1.2 |
| 77.5° | 0.6 |
| 80° | 0.6 |
| 82.5° | 0.6 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)