

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294263

Luminaire Tested: P3AS09R55W2N902765DE010 E3D1LI\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294263  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R55W2N902765DE010 E3D1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,  
E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 752.0 lumens  
Efficiency: N/A  
Efficacy: 83.6 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294263  
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3D1LI\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294263

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3D1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	218075
5°	210345
10°	217876
15°	214803
20°	198794
25°	160775
30°	96344
35°	32658
40°	8988
45°	4000
50°	1160
55°	229
60°	132
65°	156
70°	192
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4000 cd/sqm



TEST NUMBER: P1294263

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3D1LI\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.5	12.3
10°-20°	263.4	35.0
20°-30°	292.8	38.9
30°-40°	91.2	12.1
40°-50°	10.9	1.5
50°-60°	0.8	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	648.7	86.3
0°-40°	739.9	98.4
0°-60°	751.7	100.0
0°-90°	752.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	752.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	994	
5°	956	92
15°	946	263
25°	664	293
35°	122	91
45°	13	11
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294263

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3D1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	994.5
1°	990.8
2°	981.1
3°	969.1
4°	958.2
5°	955.6
6°	958.5
7°	964.5
8°	971.3
9°	976.8
10°	978.5
11°	977.3
12°	972.8
13°	965.6
14°	957.3
15°	946.2
16°	933.3
17°	917.1
18°	898.8
19°	876.8
20°	851.9
21°	823.6
22°	790.2
23°	753.4
24°	711.1
25°	664.5
26°	613.4
27°	559.1
28°	501.1
29°	441.4
30°	380.5
31°	319.4
32°	259.7
32.5°	233.1
33°	205.7
34°	159.1
35°	122.0
36°	92.8
37°	68.9
37.5°	58.9
38°	51.1
39°	38.9
40°	31.4
42.5°	20.0
45°	12.9



TEST NUMBER: P1294263

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3D1LI\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	7.7
50°	3.4
52.5°	1.1
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)