

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294302

Luminaire Tested: P3AS09R55W2N902765DE010 E3DL1LI\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294302  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R55W2N902765DE010 E3DL1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,  
E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 641.0 lumens  
Efficiency: N/A  
Efficacy: 71.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294302  
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DL1LI\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294302

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DL1LI\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.4	11.6
10°-20°	189.4	29.6
20°-30°	198.5	31.0
30°-40°	115.8	18.1
40°-50°	43.3	6.8
50°-60°	10.2	1.6
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.4	72.1
0°-40°	578.2	90.2
0°-60°	631.8	98.6
0°-90°	641.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	803	
5°	792	74
15°	685	189
25°	438	199
35°	181	116
45°	53	43
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1294302  
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DL1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	802.7
2.5°	800.3
5°	791.5
7.5°	777.4
10°	755.6
12.5°	725.1
15°	685.1
17.5°	634.5
20°	575.1
22.5°	508.7
25°	438.1
27.5°	365.8
30°	297.0
32.5°	234.6
35°	181.1
37.5°	137.6
40°	101.7
42.5°	72.9
45°	52.9
47.5°	38.2
50°	25.9
52.5°	14.7
55°	8.2
57.5°	7.1
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	2.9
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)