

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292505

Luminaire Tested: P3AS09R30W2N902750DE010 E3CB1MB_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902750DE010 E3CB1MB_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 753.0 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292505
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3CB1MB_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292505

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3CB1MB_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.2	33.4
10°-20°	391.6	52.0
20°-30°	90.9	12.1
30°-40°	14.1	1.9
40°-50°	2.4	0.3
50°-60°	1.1	0.2
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.7	97.4
0°-40°	747.8	99.3
0°-60°	751.4	99.8
0°-90°	753.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	753.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2796	
5°	2733	251
15°	1486	392
25°	157	91
35°	17	14
45°	2	2
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1292505
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3CB1MB_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2796.4
1°	2794.6
2°	2786.9
3°	2773.9
4°	2757.4
5°	2733.1
6°	2702.9
7°	2658.0
8°	2596.5
9°	2506.0
10°	2391.8
11°	2244.6
12°	2078.4
13°	1893.8
14°	1691.0
15°	1486.3
17.5°	972.4
20°	548.9
22.5°	280.3
25°	156.7
27.5°	96.4
30°	59.1
32.5°	31.9
35°	17.2
37.5°	11.2
40°	7.1
42.5°	4.1
45°	2.4
47.5°	1.8
50°	1.8
52.5°	1.2
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1292505
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3CB1MB_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)