

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292566

Luminaire Tested: P3AS09R30W2N902750DE010 E3DL1H_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902750DE010 E3DL1H_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 623.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292566
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1H_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292566

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1H_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.5	22.7
10°-20°	251.6	40.4
20°-30°	145.4	23.3
30°-40°	55.2	8.9
40°-50°	16.9	2.7
50°-60°	5.7	0.9
60°-70°	3.8	0.6
70°-80°	2.1	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.6	86.4
0°-40°	593.8	95.3
0°-60°	616.4	98.9
0°-90°	623.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	623.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1658	
5°	1572	142
15°	925	252
25°	306	145
35°	84	55
45°	21	17
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1292566
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1H_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1657.9
1°	1656.7
2°	1646.7
3°	1627.9
4°	1604.3
5°	1571.9
6°	1530.8
7°	1484.8
8°	1433.6
9°	1372.4
10°	1307.1
11°	1236.5
12°	1161.7
13°	1083.5
14°	1004.0
15°	924.6
17.5°	729.2
20°	557.9
22.5°	413.7
25°	306.0
27.5°	222.5
30°	162.4
32.5°	117.1
35°	83.6
37.5°	58.3
40°	41.2
42.5°	28.8
45°	20.6
47.5°	14.1
50°	10.0
52.5°	7.1
55°	5.9
57.5°	5.3
60°	4.7
62.5°	4.1
65°	4.1
67.5°	3.5
70°	2.9
72.5°	2.4
75°	1.8
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0



TEST NUMBER: P1292566
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1H_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)