

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294324

Luminaire Tested: P3AS09R55W2N902765DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294324
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902765DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 245.0 lumens
Efficiency: N/A
Efficacy: 27.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294324
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1294324
 CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46071
5°	45476
10°	43687
15°	40863
20°	37267
25°	33244
30°	29093
35°	24173
40°	19064
45°	12932
50°	7880
55°	4091
60°	3815
65°	3580
70°	3334
75°	2965
80°	2904
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12932 cd/sqm



TEST NUMBER: P1294324

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.4	7.9
10°-20°	50.3	20.5
20°-30°	63.0	25.7
30°-40°	56.2	23.0
40°-50°	32.9	13.4
50°-60°	11.3	4.6
60°-70°	6.9	2.8
70°-80°	3.8	1.6
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	132.7	54.2
0°-40°	188.9	77.1
0°-60°	233.2	95.2
0°-90°	245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	210	
5°	207	19
15°	180	50
25°	137	63
35°	90	56
45°	42	33
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294324
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	210.1
2.5°	208.9
5°	206.6
7.5°	202.0
10°	196.2
12.5°	189.0
15°	180.0
17.5°	170.4
20°	159.7
22.5°	148.7
25°	137.4
27.5°	126.2
30°	114.9
32.5°	102.7
35°	90.3
37.5°	78.1
40°	66.6
42.5°	54.1
45°	41.7
47.5°	31.8
50°	23.1
52.5°	15.0
55°	10.7
57.5°	9.5
60°	8.7
62.5°	7.8
65°	6.9
67.5°	6.1
70°	5.2
72.5°	4.3
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.4
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)