

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294355

Luminaire Tested: P3AS09R55W2N902765DE010 E3DLD1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294355
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902765DE010 E3DLD1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 501.0 lumens
Efficiency: N/A
Efficacy: 55.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294355
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294355

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.6	7.9
10°-20°	102.9	20.5
20°-30°	128.8	25.7
30°-40°	115.0	23.0
40°-50°	67.3	13.4
50°-60°	23.3	4.6
60°-70°	14.1	2.8
70°-80°	7.8	1.6
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	271.3	54.1
0°-40°	386.3	77.1
0°-60°	476.9	95.2
0°-90°	501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	430	
5°	422	40
15°	368	103
25°	281	129
35°	185	115
45°	85	67
55°	22	23
65°	14	14
75°	7	8
85°	2	2
90°	0	



TEST NUMBER: P1294355
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLD1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	429.6
2.5°	427.2
5°	422.5
7.5°	413.0
10°	401.2
12.5°	386.4
15°	368.1
17.5°	348.5
20°	326.6
22.5°	304.1
25°	281.1
27.5°	258.0
30°	234.9
32.5°	210.1
35°	184.6
37.5°	159.8
40°	136.1
42.5°	110.7
45°	85.2
47.5°	65.1
50°	47.3
52.5°	30.8
55°	21.9
57.5°	19.5
60°	17.8
62.5°	16.0
65°	14.2
67.5°	12.4
70°	10.7
72.5°	8.9
75°	7.1
77.5°	5.9
80°	4.7
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)