

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292658

Luminaire Tested: P3AS09R30W2N902750DE010 E3PHLP1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292658
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902750DE010 E3PHLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 328.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292658
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3PHLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292658

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3PHLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106505
5°	100418
10°	85837
15°	68786
20°	53625
25°	40333
30°	29422
35°	20719
40°	14227
45°	10172
50°	8324
55°	8028
60°	8113
65°	8302
70°	8655
75°	9235
80°	9597
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 11256 cd/sqm



TEST NUMBER: P1292658

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3PHLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.3	12.6
10°-20°	84.2	25.7
20°-30°	76.7	23.4
30°-40°	48.8	14.9
40°-50°	26.1	8.0
50°-60°	19.1	5.8
60°-70°	16.1	4.9
70°-80°	11.2	3.4
80°-90°	4.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.2	61.6
0°-40°	251.0	76.5
0°-60°	296.3	90.3
0°-90°	328.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	328.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	486	
5°	456	41
15°	303	84
25°	167	77
35°	77	49
45°	33	26
55°	21	19
65°	16	16
75°	11	11
85°	4	4
90°	0	



TEST NUMBER: P1292658

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3PHLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	485.7
2.5°	478.1
5°	456.2
7.5°	424.2
10°	385.5
12.5°	344.3
15°	303.0
17.5°	265.1
20°	229.8
22.5°	197.0
25°	166.7
27.5°	139.7
30°	116.2
32.5°	94.3
35°	77.4
37.5°	61.4
40°	49.7
42.5°	39.6
45°	32.8
47.5°	26.9
50°	24.4
52.5°	22.7
55°	21.0
57.5°	20.2
60°	18.5
62.5°	17.7
65°	16.0
67.5°	15.2
70°	13.5
72.5°	11.8
75°	10.9
77.5°	9.3
80°	7.6
82.5°	6.7
85°	4.2
87.5°	1.7
90°	0.0

(END OF REPORT)