

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294485

Luminaire Tested: P3AS09R60W2N902750DE010 E3DLD1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902750DE010 E3DLD1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 481.0 lumens
Efficiency: N/A
Efficacy: 53.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294485
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294485
 CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	85388
5°	84415
10°	81495
15°	77004
20°	70986
25°	64262
30°	57047
35°	48747
40°	38758
45°	27352
50°	16341
55°	8258
60°	7938
65°	7264
70°	6732
75°	6439
80°	5935
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27352 cd/sqm



TEST NUMBER: P1294485

CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.0	7.5
10°-20°	94.8	19.7
20°-30°	121.7	25.3
30°-40°	112.8	23.5
40°-50°	68.7	14.3
50°-60°	22.9	4.8
60°-70°	13.9	2.9
70°-80°	7.9	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	252.5	52.5
0°-40°	365.4	76.0
0°-60°	457.0	95.0
0°-90°	481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	481.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	389	
5°	384	36
15°	339	95
25°	266	122
35°	182	113
45°	88	69
55°	22	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1294485
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLD1H_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	389.4
2.5°	387.6
5°	383.5
7.5°	376.0
10°	366.0
12.5°	353.8
15°	339.2
17.5°	322.2
20°	304.2
22.5°	284.9
25°	265.6
27.5°	245.8
30°	225.3
32.5°	204.9
35°	182.1
37.5°	158.2
40°	135.4
42.5°	111.5
45°	88.2
47.5°	68.3
50°	47.9
52.5°	28.6
55°	21.6
57.5°	19.8
60°	18.1
62.5°	15.8
65°	14.0
67.5°	12.3
70°	10.5
72.5°	8.8
75°	7.6
77.5°	5.8
80°	4.7
82.5°	2.9
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)