

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292705

Luminaire Tested: P3AS09R30W2N902765DE010 E3D1LI\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292705  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902765DE010 E3D1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 736.0 lumens  
Efficiency: N/A  
Efficacy: 81.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292705  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1LI\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292705

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 98 | 100 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96 | 95 | 94  |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  | 100 | 98  | 97  | 97  | 96  | 95  | 94  | 93 | 92 | 90  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 90  | 89 | 88 | 85  |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 93  | 91  | 89  | 88  | 86 | 85 | 82  |
| 5   | 101 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 87  | 92  | 89  | 87  | 90  | 88  | 86  | 85  | 84 | 83 | 82  |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 82  | 81 | 80 | 78  |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 80  | 79 | 78 | 76  |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 78  | 77 | 76 | 74  |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 79  | 77  | 82  | 79  | 77  | 76  | 75 | 74 | 72  |
| 10  | 88  | 82  | 78  | 75  | 88  | 81  | 78  | 75  | 81  | 77  | 75  | 80  | 77  | 75  | 80  | 77  | 75  | 74  | 73 | 72 | 70  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 585589 |
| 5°  | 577943 |
| 10° | 504600 |
| 15° | 320728 |
| 20° | 127084 |
| 25° | 42438  |
| 30° | 19750  |
| 35° | 8941   |
| 40° | 3435   |
| 45° | 1675   |
| 50° | 478    |
| 55° | 229    |
| 60° | 132    |
| 65° | 156    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1675 cd/sqm



TEST NUMBER: P1292705

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1LI\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 240.1  | 32.6      |
| 10°-20°   | 372.3  | 50.6      |
| 20°-30°   | 96.0   | 13.0      |
| 30°-40°   | 22.5   | 3.1       |
| 40°-50°   | 4.4    | 0.6       |
| 50°-60°   | 0.5    | 0.1       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 708.3  | 96.2      |
| 0°-40°    | 730.8  | 99.3      |
| 0°-60°    | 735.7  | 100.0     |
| 0°-90°    | 736.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 736.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2670 |      |
| 5°  | 2626 | 240  |
| 15° | 1413 | 372  |
| 25° | 175  | 96   |
| 35° | 33   | 23   |
| 45° | 5    | 4    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1292705

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2670.5 |
| 1°    | 2668.5 |
| 2°    | 2662.2 |
| 3°    | 2655.0 |
| 4°    | 2644.5 |
| 5°    | 2625.6 |
| 6°    | 2595.1 |
| 7°    | 2544.2 |
| 8°    | 2474.8 |
| 9°    | 2384.2 |
| 10°   | 2266.2 |
| 11°   | 2125.9 |
| 12°   | 1972.8 |
| 13°   | 1796.5 |
| 14°   | 1611.9 |
| 15°   | 1412.8 |
| 16°   | 1217.7 |
| 17°   | 1029.7 |
| 18°   | 849.4  |
| 19°   | 684.0  |
| 20°   | 544.6  |
| 21°   | 428.6  |
| 22°   | 337.1  |
| 23°   | 266.8  |
| 24°   | 213.7  |
| 25°   | 175.4  |
| 26°   | 146.3  |
| 27°   | 124.3  |
| 28°   | 107.4  |
| 29°   | 92.0   |
| 30°   | 78.0   |
| 32.5° | 49.1   |
| 35°   | 33.4   |
| 37.5° | 20.9   |
| 40°   | 12.0   |
| 42.5° | 8.0    |
| 45°   | 5.4    |
| 47.5° | 3.1    |
| 50°   | 1.4    |
| 52.5° | 0.6    |
| 55°   | 0.6    |
| 57.5° | 0.3    |
| 60°   | 0.3    |
| 62.5° | 0.3    |
| 65°   | 0.3    |



TEST NUMBER: P1292705  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1LI\_3000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.3 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)