

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292727

Luminaire Tested: P3AS09R30W2N902765DE010 E3D1WMH\_6500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292727  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902765DE010 E3D1WMH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 743.0 lumens  
Efficiency: N/A  
Efficacy: 82.6 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292727  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1WMH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292727

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1WMH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	95	93	92	90
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	93	91	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	90	88	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	88	85	83	82
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	86	83	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	84	81	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	82	79	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	80	77	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	80	77	75	74

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	591159
5°	583446
10°	509409
15°	323770
20°	128274
25°	42849
30°	19927
35°	9021
40°	3464
45°	1706
50°	478
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1706 cd/sqm



TEST NUMBER: P1292727

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1WMH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.3	32.6
10°-20°	375.8	50.6
20°-30°	96.9	13.0
30°-40°	22.8	3.1
40°-50°	4.5	0.6
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.0	96.2
0°-40°	737.8	99.3
0°-60°	742.8	100.0
0°-90°	743.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	743.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2696	
5°	2651	242
15°	1426	376
25°	177	97
35°	34	23
45°	6	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1292727

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1WMH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2695.9
1°	2693.9
2°	2687.5
3°	2680.3
4°	2669.6
5°	2650.6
6°	2619.7
7°	2568.4
8°	2498.3
9°	2406.9
10°	2287.8
11°	2146.1
12°	1991.6
13°	1813.6
14°	1627.3
15°	1426.2
16°	1229.3
17°	1039.5
18°	857.5
19°	690.5
20°	549.7
21°	432.6
22°	340.3
23°	269.4
24°	215.7
25°	177.1
26°	147.7
27°	125.5
28°	108.4
29°	92.9
30°	78.7
32.5°	49.6
35°	33.7
37.5°	21.1
40°	12.1
42.5°	8.1
45°	5.5
47.5°	3.2
50°	1.4
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3



TEST NUMBER: P1292727  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3D1WMH\_6500K

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)