

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294598

Luminaire Tested: P3AS09R60W2N902765DE010 E3D1WH_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294598
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902765DE010 E3D1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 6500K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 705.0 lumens
Efficiency: N/A
Efficacy: 78.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294598
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3D1WH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1294598
 CATALOG NUMBER: P3AS09R60W2N902765DE010 E3D1WH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67			
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63			
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184722
5°	174378
10°	169848
15°	165971
20°	154317
25°	137935
30°	105358
35°	60846
40°	23616
45°	9830
50°	2149
55°	344
60°	263
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9830 cd/sqm



TEST NUMBER: P1294598

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3D1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.8	10.6
10°-20°	203.6	28.9
20°-30°	255.1	36.2
30°-40°	142.6	20.2
40°-50°	27.1	3.8
50°-60°	1.4	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.5	75.7
0°-40°	676.1	95.9
0°-60°	704.6	99.9
0°-90°	705.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	705.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	842	
5°	792	75
15°	731	204
25°	570	255
35°	227	143
45°	32	27
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294598
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3D1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	842.4
1°	838.9
2°	828.0
3°	815.0
4°	802.9
5°	792.2
6°	784.1
7°	777.2
8°	772.0
9°	767.1
10°	762.8
11°	758.5
12°	753.6
13°	747.5
14°	740.3
15°	731.1
16°	719.8
17°	707.1
18°	692.7
19°	676.3
20°	661.3
21°	645.1
22°	628.4
23°	610.8
24°	591.5
25°	570.1
26°	545.1
27°	517.1
28°	485.7
29°	452.2
30°	416.1
31°	379.8
32°	342.3
32.5°	321.8
33°	303.4
34°	265.0
35°	227.3
36°	193.2
37°	157.2
37.5°	140.7
38°	124.6
39°	100.4
40°	82.5
42.5°	50.2
45°	31.7



TEST NUMBER: P1294598
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3D1WH_6500K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	17.6
50°	6.3
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)