

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294606

Luminaire Tested: P3AS09R60W2N902765DE010 E3DL1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294606  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R60W2N902765DE010 E3DL1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 301.0 lumens  
Efficiency: N/A  
Efficacy: 33.4 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294606  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294606  
 CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73			73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48			48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	71069
5°	70394
10°	68358
15°	64041
20°	56682
25°	47422
30°	37170
35°	26957
40°	17948
45°	11164
50°	6038
55°	1759
60°	1623
65°	1505
70°	1475
75°	1440
80°	1389
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11164 cd/sqm



TEST NUMBER: P1294606

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	30.1	10.0
10°-20°	78.3	26.0
20°-30°	89.2	29.6
30°-40°	63.3	21.0
40°-50°	28.7	9.5
50°-60°	6.1	2.0
60°-70°	2.9	1.0
70°-80°	1.8	0.6
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	197.6	65.6
0°-40°	260.9	86.7
0°-60°	295.7	98.2
0°-90°	301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	301.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	324	
5°	320	30
15°	282	78
25°	196	89
35°	101	63
45°	36	29
55°	5	6
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1294606  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DL1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	324.1
2.5°	323.0
5°	319.8
7.5°	314.4
10°	307.0
12.5°	296.4
15°	282.1
17.5°	264.1
20°	242.9
22.5°	220.0
25°	196.0
27.5°	171.4
30°	146.8
32.5°	123.3
35°	100.7
37.5°	80.7
40°	62.7
42.5°	47.5
45°	36.0
47.5°	26.9
50°	17.7
52.5°	8.3
55°	4.6
57.5°	4.0
60°	3.7
62.5°	3.4
65°	2.9
67.5°	2.6
70°	2.3
72.5°	2.0
75°	1.7
77.5°	1.4
80°	1.1
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)