

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292802

Luminaire Tested: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292802  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 187.0 lumens  
Efficiency: N/A  
Efficacy: 20.8 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292802  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292802  
 CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 95  | 93  | 93  | 93  | 93  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  | 94  | 92  | 90  | 92  | 90  | 88  | 86  | 86  | 86  | 86  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  | 89  | 86  | 83  | 87  | 84  | 82  | 80  | 80  | 80  | 80  |
| 4   | 97  | 89  | 84  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  | 74  | 74  | 74  |
| 5   | 92  | 84  | 78  | 73  | 90  | 83  | 77  | 73  | 81  | 76  | 72  | 79  | 75  | 72  | 78  | 74  | 71  | 70  | 70  | 70  | 70  |
| 6   | 88  | 79  | 73  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 65  | 65  | 65  | 65  |
| 7   | 83  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 63  | 71  | 67  | 63  | 70  | 66  | 63  | 61  | 61  | 61  | 61  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  | 68  | 63  | 60  | 67  | 62  | 59  | 58  | 58  | 58  | 58  |
| 9   | 76  | 67  | 61  | 57  | 75  | 66  | 60  | 57  | 65  | 60  | 56  | 64  | 60  | 56  | 63  | 59  | 56  | 55  | 55  | 55  | 55  |
| 10  | 73  | 63  | 58  | 54  | 72  | 63  | 57  | 54  | 62  | 57  | 54  | 61  | 57  | 53  | 61  | 56  | 53  | 52  | 52  | 52  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 63898 |
| 5°  | 61919 |
| 10° | 55777 |
| 15° | 46152 |
| 20° | 35726 |
| 25° | 26808 |
| 30° | 19446 |
| 35° | 12956 |
| 40° | 7958  |
| 45° | 4683  |
| 50° | 2866  |
| 55° | 2332  |
| 60° | 2017  |
| 65° | 1660  |
| 70° | 1475  |
| 75° | 1440  |
| 80° | 1137  |
| 85° | 1510  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4683 cd/sqm



TEST NUMBER: P1292802

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 25.9   | 13.8      |
| 10°-20°   | 56.0   | 29.9      |
| 20°-30°   | 50.9   | 27.2      |
| 30°-40°   | 30.8   | 16.5      |
| 40°-50°   | 12.3   | 6.6       |
| 50°-60°   | 5.5    | 2.9       |
| 60°-70°   | 3.3    | 1.8       |
| 70°-80°   | 1.8    | 0.9       |
| 80°-90°   | 0.5    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 132.8  | 71.0      |
| 0°-40°    | 163.6  | 87.5      |
| 0°-60°    | 181.4  | 97.0      |
| 0°-90°    | 187.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 187.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 291 |      |
| 5°  | 281 | 26   |
| 15° | 203 | 56   |
| 25° | 111 | 51   |
| 35° | 48  | 31   |
| 45° | 15  | 12   |
| 55° | 6   | 5    |
| 65° | 3   | 3    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1292802  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 291.4 |
| 1°    | 291.1 |
| 2°    | 290.0 |
| 3°    | 287.9 |
| 4°    | 285.0 |
| 5°    | 281.3 |
| 6°    | 276.6 |
| 7°    | 271.7 |
| 8°    | 265.3 |
| 9°    | 258.1 |
| 10°   | 250.5 |
| 11°   | 241.8 |
| 12°   | 232.6 |
| 13°   | 223.3 |
| 14°   | 213.1 |
| 15°   | 203.3 |
| 17.5° | 177.5 |
| 20°   | 153.1 |
| 22.5° | 130.5 |
| 25°   | 110.8 |
| 27.5° | 92.8  |
| 30°   | 76.8  |
| 32.5° | 62.1  |
| 35°   | 48.4  |
| 37.5° | 37.1  |
| 40°   | 27.8  |
| 42.5° | 20.3  |
| 45°   | 15.1  |
| 47.5° | 11.3  |
| 50°   | 8.4   |
| 52.5° | 6.7   |
| 55°   | 6.1   |
| 57.5° | 5.2   |
| 60°   | 4.6   |
| 62.5° | 3.8   |
| 65°   | 3.2   |
| 67.5° | 2.9   |
| 70°   | 2.3   |
| 72.5° | 2.0   |
| 75°   | 1.7   |
| 77.5° | 1.4   |
| 80°   | 0.9   |
| 82.5° | 0.6   |
| 85°   | 0.6   |
| 87.5° | 0.3   |



TEST NUMBER: P1292802  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1GPH\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)