

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292818

Luminaire Tested: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292818  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 341.0 lumens  
Efficiency: N/A  
Efficacy: 37.9 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292818  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292818  
 CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	116526
5°	112899
10°	101713
15°	84155
20°	65152
25°	48874
30°	35474
35°	23637
40°	14542
45°	8528
50°	5219
55°	4244
60°	3728
65°	3009
70°	2693
75°	2711
80°	2020
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8528 cd/sqm



TEST NUMBER: P1292818

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.2	13.8
10°-20°	102.1	29.9
20°-30°	92.9	27.2
30°-40°	56.2	16.5
40°-50°	22.5	6.6
50°-60°	10.0	2.9
60°-70°	6.0	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.1	71.0
0°-40°	298.3	87.5
0°-60°	330.8	97.0
0°-90°	341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	531	
5°	513	47
15°	371	102
25°	202	93
35°	88	56
45°	28	23
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292818  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	531.4
1°	530.9
2°	528.8
3°	525.1
4°	519.8
5°	512.9
6°	504.4
7°	495.4
8°	483.8
9°	470.6
10°	456.8
11°	441.0
12°	424.1
13°	407.1
14°	388.6
15°	370.7
17.5°	323.6
20°	279.2
22.5°	237.9
25°	202.0
27.5°	169.2
30°	140.1
32.5°	113.2
35°	88.3
37.5°	67.7
40°	50.8
42.5°	37.0
45°	27.5
47.5°	20.6
50°	15.3
52.5°	12.2
55°	11.1
57.5°	9.5
60°	8.5
62.5°	6.9
65°	5.8
67.5°	5.3
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.6
80°	1.6
82.5°	1.1
85°	1.1
87.5°	0.5



TEST NUMBER: P1292818  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLP1MW\_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)