

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294725

Luminaire Tested: P3AS09R65W2N902750DE010 E3CB1MW\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902750DE010 E3CB1MW\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,  
E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 732.1 lumens  
Efficiency: N/A  
Efficacy: 81.3 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294725  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3CB1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1294725  
 CATALOG NUMBER: P3AS09R65W2N902750DE010 E3CB1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93	93	93	93
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	178889
5°	168368
10°	166218
15°	163293
20°	154177
25°	143089
30°	111232
35°	64353
40°	25934
45°	11939
50°	4640
55°	1797
60°	1579
65°	1557
70°	1539
75°	1525
80°	1515
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11939 cd/sqm



TEST NUMBER: P1294725

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3CB1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.7	9.9
10°-20°	200.9	27.4
20°-30°	262.9	35.9
30°-40°	152.3	20.8
40°-50°	32.6	4.5
50°-60°	5.3	0.7
60°-70°	3.0	0.4
70°-80°	1.7	0.2
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.5	73.3
0°-40°	688.8	94.1
0°-60°	726.7	99.3
0°-90°	732.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	732.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	816	
5°	765	73
15°	719	201
25°	591	263
35°	240	152
45°	38	33
55°	5	5
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1294725  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3CB1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	815.8
2.5°	792.7
5°	764.9
7.5°	753.6
10°	746.5
12.5°	736.5
15°	719.3
17.5°	692.6
20°	660.7
22.5°	630.5
25°	591.4
27.5°	525.7
30°	439.3
32.5°	340.4
35°	240.4
37.5°	152.1
40°	90.6
42.5°	56.8
45°	38.5
47.5°	24.9
50°	13.6
52.5°	6.5
55°	4.7
57.5°	4.1
60°	3.6
62.5°	3.6
65°	3.0
67.5°	2.4
70°	2.4
72.5°	1.8
75°	1.8
77.5°	1.2
80°	1.2
82.5°	0.6
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)