

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294759

Luminaire Tested: P3AS09R65W2N902750DE010 E3D1WH\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294759  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902750DE010 E3D1WH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 695.0 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294759  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WH\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294759

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.1	10.7
10°-20°	197.8	28.5
20°-30°	250.3	36.0
30°-40°	142.6	20.5
40°-50°	28.3	4.1
50°-60°	1.5	0.2
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	522.2	75.1
0°-40°	664.8	95.6
0°-60°	694.6	99.9
0°-90°	695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	849	
5°	786	74
15°	710	198
25°	561	250
35°	227	143
45°	33	28
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1294759  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	849.3
1°	843.0
2°	829.3
3°	813.3
4°	797.6
5°	785.6
6°	776.7
7°	769.6
8°	763.3
9°	757.0
10°	751.0
11°	744.4
12°	737.6
13°	729.3
14°	720.4
15°	709.9
16°	697.3
17°	683.6
18°	668.7
19°	653.0
20°	638.5
21°	623.6
22°	610.2
23°	596.2
24°	579.9
25°	561.0
26°	538.5
27°	511.3
28°	480.8
29°	448.2
30°	414.2
31°	376.8
32°	339.7
32.5°	320.5
33°	301.9
34°	264.2
35°	227.1
36°	192.8
37°	158.8
37.5°	141.4
38°	127.4
39°	103.1
40°	84.3
42.5°	52.0
45°	33.1



TEST NUMBER: P1294759  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3D1WH\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	19.4
50°	7.1
52.5°	1.4
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)